

Product Name :
Astra Scientific Radius Bending Machine

Product Code :
ASTSTEEL-0012



Description :

Astra Scientific Radius Bending Machine

Technical Specification :

Descriptions:

Heavy-duty Radius Bar Bending Machine will radius up to 36mm rebar. RB 36 comes with a standard 2-speed drive motor, adhering to most safety requirements it is an efficient and quicker bender used for making circular rings.

Radius Bender is designed to bend radius rebar without the need to pre-bend the end of the bar. Keeping the operator's hands away from the forming rolls allows safe operation. The Radius Bender has been designed with a guard for making rings in a safe operation. After forming the ring, the finished shape is lifted out of the machine while the guard hinges and returns to the closed position. The drive rollers do not rotate while the guard is open.

Technical Specifications:

LB 36 LB 42

28 mm bar 32 mm bar

Grade 60 or 65kg/mm2

Feed Motor

3hp 2-speed motor Feed Motor

5hp motor

440 VAC 3-Phase 50Hz Standard

44 Meters/Minute or 22 meters/minute 22 Meters/Minute

1001x1050x930 mm 1001x1050x930 mm

700 Kgs 750 kgs



Astra Scientific

www.astrascientific.com, **Email:** info@astrascientific.com

Address: K-88, 20th Street, Annanagar, Chennai, India – 600040 **Phone:** +91-8860605265