

Product Name :
Lux Meter

Product Code :
MEASUREMENT SUK-
AS03LAB020



Description :

Lux Meter

Technical Specification :

A lux meter is equipment that measures brightness of falling on an object at a particular area. In other words, it properly gauges the intensity at which brightness appears to the human eye. We are engaged in offering Lux Meter, Measures Illumination with 3 Ranges. Ranges from 0 – 50 000 Lux. LCD display and Low Battery Indication.

FEATURES:

- 4000 counts with bar graph 61 segments
- Auto-ranging
- Automatic power off
- User selectable FC/Lux
- Peak hold
- Battery power indication
- Maximum data hold

SPECIFICATION:

- Power Source: 1×9.0V
- Accuracy: +5 percent of reading
- Receiving Light: Silicon of photo electricity diod
- Standard Accessories: Soft carrying case, manual
- Dimension Photo Detector: 82 (H) x 55 (W) x 7 (D) millimeter;

Meter Body: 148 (H) x 70 (W) x 40 (D) millimeter



Astra Scientific

www.astrascientific.com, **Email:** info@astrascientific.com

Address: K-88, 20th Street, Annanagar, Chennai, India – 600040 **Phone:** +91-8860605265