

**Product Name :**  
Series Mechatronics Training System

**Product Code :**  
AUT-LABAST-003



**Description :**

Series Mechatronics Training System, We are manufacturer, supplier, exporter and solution provider in quality Series Mechatronics Training System

**Technical Specification :**

Series Mechatronics Training System Since PLC (Programmable Logic Controller) was first introduced in 1970, it has been widely applied to various industrial uses such as machine and process controls.

The Modular Production System stations allow varying simulation of real production processes that exist in industry field. The system is universal, industry-based, modular and flexible for further expansion. Students can learn the entire process of production such as feeding, processing, etc...

Each station simplifies the training of operation and can be expanded sequentially step by step through building complex automated procedure.- Input-simulation switches function as level and pulse Input for different input signal.

- Easy-to-use windows-based development software
- With various peripheral devices and devices that support external extensions particularly suits laboratory experiment and project implementation.
- With various simulations I/O devices for studying and observing the results
- Use 4mm safety sockets Input/Output terminals to ensure the physical

safety of users.  
The stations are universal, industry-based.

---



## **Astra Scientific**

www.astrascientific.com, **Email:** info@astrascientific.com

**Address:** K-88, 20th Street, Annanagar, Chennai, India – 600040 **Phone:** +91-8860605265