

Product Name :
Soil Extruder Motor Operated

Product Code :
ASTSOIL-0038



Description :

Soil Extruder Motor Operated

Technical Specification :

Soil extruder, motor operated: geotechnical engineering lab equipment, Features one of the largest capacities available on the market (ram stroke 900 mm), and due to the large number of standard adaptors, is considered the most versatile extruder. The machine exerts a max. thrust of 60 kN and is very simple to operate: a lever controls the extruding speed and the hydraulic.



Astra Scientific

www.astrascientific.com, **Email:** info@astrascientific.com

Address: K-88, 20th Street, Annanagar, Chennai, India – 600040 **Phone:** +91-8860605265