

Product Name :
Multi Turbine Test Rig

Product Code :
TOURBO SUK-AS03LAB011



Description :

Multi Turbine Test Rig

Technical Specification :

The designed and developed self-contained, mobile unit of multiple types of turbines including Pelton, Francis, Kaplan and/or Cross Flow. Designed for study of turbine characteristics under various flow rates and heads. Includes pump, storage tanks, turbine units connected in parallel, dynamometer for each turbine, and instrumentation for measuring flow rate, speed, and torque.

The speed is captured by means of an inductive, non-contact position sensor at the turbine shaft. For determining the turbine power, the eddy current brake is equipped with a force sensor for torque measurement. The pressures at the inlet and outlet of the turbine, the temperature and the flow rate are recorded with sensors. The recorded measured values are displayed digitally and processed further in a PC. The PC is used to calculate the power output data of the examined turbine and to represent them in characteristic curves.

FEATURES:

- Supply unit for turbine.
- Closed water circuit contains multistage centrifugal pump, tank, and inductive flow meter and flow control valve.

- Connection to the turbines via flexible hose with quick-release coupling.
- Constant torques and speeds can be adjusted.
- Digital display for flow rate, pressure and temperature.
- Braking torque and speed measured.
- Torque vs. speed at various heads and flow rates.
- Power output vs. speed for various heads and flow rates.
- Efficiency vs. speed for a given head and flow rate.
- Racing characteristics

SPECIFICATIONS:

- Pelton turbine:

Construction: Stainless steel runner and nozzle.

Stainless steel casing with transparent window to observe hydraulic action.

Maximum power: 400 W of brake power.

- Francis turbine:

Construction: Metal runner: Non-corrosion metal

Casing with adjustable guide vanes and transparent window to observe guide vane position.

Maximum power: 400 W of brake power.

- Cross Flow turbine:

Construction: Stainless steel runner, and nozzle.

Stainless steel casing with transparent window.

Maximum power: 400 W of brake power.

- Pump: 2.2kw.
- Dynamometer: Water brake absorber.
- Measuring instruments:

Torques: Spring balances absorber.

Pressures: Pressure gauges at turbine inlets.

Sensors with digital display: Flow rate and speeds.

- Power supply: 220 V, 1Ph, 50 Hz.

DIMENSIONS AND WEIGHT:

- LxWxH: 2800 x 960 x 1500 mm
- 380 kg



Astra Scientific

www.astrascientific.com, **Email:** info@astrascientific.com

Address: K-88, 20th Street, Annanagar, Chennai, India – 600040 **Phone:** +91-8860605265