

Product Name :
Dry Cleaning Apparatus

Product Code :
FABRIC SUK-AS03LAB013



Description :

Dry Cleaning Apparatus

Technical Specification :

The Dry Cleaning Apparatus consists of a motor driven corrosion resistant stainless steel tumbler, which rotates around an axis 50° inclined to tumbler axis at approximately 45 rpm. The tumbler is also provided with a stainless steel cover with a rubber seal and a quick acting positive clamp. The tumbler is rotated with the help of an electric motor through pulley-belt, reduction gearbox, and chain and sprocket drive.

A pre-set type digital timer of 999 minutes is provided to indicate the actual run time and also to stop the motor after a pre-set time interval.

The equipment is built on a sturdy fabricated table type structure with lockable storage space for keeping the samples.

The
apparatus is finished in shore blue metallic painting and bright chrome
/ zinc plating to give it a corrosion resistant finish.



Astra Scientific

www.astrascientific.com, **Email:** info@astrascientific.com

Address: K-88, 20th Street, Annanagar, Chennai, India – 600040 **Phone:** +91-8860605265