

<b>Product Name :</b> Button Snap Pull Tester	<b>Product Code :</b> FABRIC SUK-AS03LAB015
--	--



**Description :**

Button Snap Pull Tester

**Technical Specification :**

- Material  
Metal
- Power Source  
Electric
- Weight  
20-50 Kilograms (kg)
- Usage

## Buttons, rivets and joints

With an aim to be a market leader in our domain, we are growing as one of the trusted manufacturers and exporters of Button Snap Pull Tester.

Utilized in garments industry, it is required for testing snap strength of buttons particularly babies cloth. This tester is also used to test strength of rivets and joints to assure optimum safety & tolerance levels. Button Snap Pull Tester consists of a push-pull force gauge, vertical stand, base, and button pull fixture.

### Features:

- Equipped with a force measuring device
- Provided with two clamps where one is for holding garment and another for snap component
- Simple operation

## Button Snap Pull Tester

The equipment comprises of

- IMADA Push-Pull force gauge of 20 kgf.
- Vertical stand to hold the gauge with arrangement to change the position of Gauge.
- Base which houses the frame to grip the attachment
- Button Pull Fixture “ Connected with force gauge.

Suitable to grip buttons from 5 mm to 25 mm.

The needle in the gauge stops at the breaking load.

### Technical specification

ASTM D579-96

Automation Grade
Material
CFR-50r53



**Astra Scientific**

www.astrascientific.com, **Email:** info@astrascientific.com  
**Address:** K-88, 20th Street, Annanagar, Chennai, India – 600040 **Phone:** +91-8860605265