

Product Name :
Foam Thickness Gauge

Product Code :
FOAM SUK-AS03LAB007



Description :

Foam Thickness Gauge

Technical Specification :

Blessed and supported by the team of adroit professionals, our company is considered as one of the eminent manufacturers, suppliers and exporters of Foam Thickness Gauge.

We source high end quality materials and components from trusted vendors for manufacturing these thickness gauges as per international quality standards and norms. Available in various specifications, these equipments are broadly used to measure the thickness of the foam. High accuracy, durability and negligible maintenance are the distinguished features of our Foam Thickness Gauge.

Further details:

The GLOBE Thickness Gauge for flexible polyurethane foam consists of a dial indicator fitted on a metallic frame and a round indenter of specified size and weight to apply a specified pressure on the test specimen.

The

reading is taken after a low voltage electric contact is made between the indenter and tip of the dial indicator. An LED indicator is provided to indicate the making of the contact. The electrical contact system is operated with the help of two penlight cells. This arrangement ensures that the force exerted by the spring of the dial indicator is not transferred to the indenter, thus avoiding any error in measurement of the thickness.

A set of metallic spacers having ground ends is provided to find the thickness of specimens of up to 150 mm thickness.



Astra Scientific

www.astrascientific.com, **Email:** info@astrascientific.com

Address: K-88, 20th Street, Annanagar, Chennai, India – 600040 **Phone:** +91-8860605265