

**Product Name :**  
Astra Circulating Water Vacuum Pump

**Product Code :**  
ASTRALAB-SUPPLYA7005



**Description :**

Astra Circulating Water Vacuum Pump

**Technical Specification :**

Circulating water vacuum pumps are used in many industrial sectors such as petroleum, chemical industry, machinery, mining, light industry, medicine and food. In many processes of industrial production, such as vacuum filtration, vacuum water diversion, vacuum feeding, vacuum evaporation, vacuum concentration, vacuum rehydration and vacuum degassing, water ring pumps are widely used.

With 110V/50Hz and 110V/60Hz, the size is 400mm \* 280 \* 420.

It has the advantages of corrosion resistance, low noise and stable performance.

Good water saving effect.

Multi-function multi-function application.

Corrosion resistance, no pollution.

Novel appearance and easy operation.

The machine has low operating noise and stable performance.



## Astra Scientific

www.astrascientific.com, **Email:** info@astrascientific.com

**Address:** K-88, 20th Street, Annanagar, Chennai, India – 600040 **Phone:** +91-8860605265