

Product Name :
Circulating Water Tunnel

Product Code :
ASTRALAB-SUPPLYA38001



Description :

Circulating Water Tunnel

Technical Specification :

Breadth of the measuring section 1.4 m

Maximum water depth in the measuring section 0.84 m

The false floor of the measuring section can be shifted in height so that the water depth can be reduced down to 0.02 m

Maximum water speed in the measuring section, approx. 5.5m/s

Maximum power of the Impeller Drive 74 kW

Height between middle of measuring section and middle of lower horizontal part of the circulating water channel 3.00 m

Total height (not including a de-aeration container) 5.68 m

Total length 16.18 m



Astra Scientific

www.astrascientific.com, **Email:** info@astrascientific.com

Address: K-88, 20th Street, Annanagar, Chennai, India – 600040 **Phone:** +91-8860605265