

**Product Name :**  
DC Welding Machine 140

**Product Code :**  
ASART55



**Description :**

DC Welding Machine 140 MMA DC hand electrode welderMain Features:

1. Adopt with advanced MOSFET/IGBT inverter technology, save energy, protect the environment, light and compact, portable, accord with EMC standard.
2. Current can be adjusted stepless, high efficiency.
3. Fan-cooled, automatic protection of over-voltage and over-current, thermostatic protection, moveable welding cable.
4. Strong welding permeability, less splash, good weld appearance, sound-proof.
5. Suitable for all kinds of basic and acid electrodes.
6. Be able to long-distance weld all kinds of material, such as stainless steel, steel, tungsten, titanium, nickel and other alloy material.
7. With complete accessories.
8. Carton box/BMC.



**Astra Scientific**

www.astrascientific.com, **Email:** info@astrascientific.com

**Address:** K-88, 20th Street, Annanagar, Chennai, India – 600040 **Phone:** +91-8860605265