

Product Name :
Concrete Covermeter

Product Code :
ASTConcrete-0031



Description :

Concrete Covermeter

Technical Specification :

Introduction: Used to measure the thickness of concrete cover over steel reinforcement bars and metal pipes, furthermore it is also used to identify the location, orientation and diameter of reinforcement bars (rebar). The basic unit can be completed with a number of optional probes for various determination. See accessories.

Description: The Bartracker, which use the Pulse induction technique, features a rugged waterproof IP 65 case with a probe storage for easy portability. The battery pack can be recharged inside or outside the gauge. The display screen shows you everything you need to know.

The gauge is supplied complete with:

- Main unit
- Standard search head to meet most of measurement requirements to identify 40 mm dia. bar up to 95 mm depth (approx.), 8 mm dia. bar up to 70 mm depth (approx.), sensing area 120x60 mm.
- PC cable

- Battery pack and charger
- Shoulder strap
- Earphone
- Carry case and instruction manual



Astra Scientific

www.astrascientific.com, **Email:** info@astrascientific.com

Address: K-88, 20th Street, Annanagar, Chennai, India – 600040 **Phone:** +91-8860605265