

Product Name :
Cementometer Moisture Meter

Product Code :
ASTConcrete-0054



Description :

Cementometer Moisture Meter

Technical Specification :

- Fast and easy to use; simply insert the prongs into the material being tested
- Accurate
- Completely Portable
- Full range of water cement ratio's Instantaneous readings

The Cementometer represents a break-through in modern moisture measurement technology. By utilizing the latest microwave and microprocessor science, the Cementometer can determine the moisture content of freshly mixed cement, concrete, and mortar. Simply insert the prongs of the probe into the material to be measured and instantaneously the water cement ratio is shown on the easy to read display.

The Cementometer Microwave moisture meter uses a two prong sensor to measure the complex dielectric constant of the material in contact with the prongs. As the dielectric constant of water is four to eight times greater than most aggregates and cements, changes in water content

directly effect the sensor output. An average of five to ten readings is normally taken in order to ensure a valid reading. This output is then converted by the integrated microprocessor and moisture content is displayed directly.

Two units are available to encompass the full range of water cement ratio's found in wet concrete. The Cementometer Type R handles normal water cement ratio's with its two prong probe. The range of this instrument is approximately 0.35 to 0.65water/cement. Cementometer Type L™ handles low water/cement ratio's with its five prong probe. The range of this instrument is approximately 0.25 to 0.5 water cements. The units come calibrated for standard type I, II, and III cements. It can also be programmed with up to ten different mix design by the user. For highest accuracy, the user should program the unit for the material being used. The Cementometer Type R™ has simple to use calibration process that rapidly creates the user programs without the need for external computing devices. Finally, the Cementometer can store over 150 readings. Storage is complete with the time and date for future reference. Data can be recalled via USB interface to a personal computer running the Cementometer software.



Astra Scientific

www.astrascientific.com, **Email:** info@astrascientific.com

Address: K-88, 20th Street, Annanagar, Chennai, India – 600040 **Phone:** +91-8860605265